

PREMIUM Certificate

no. c6210a-20

Customer:

CommScope INC. 1100 CommScope Place SE 28603 Hickory, North Carolina, USA

Test sample(s):

Balanced cable: **NETCONNECT Installation Cable CS44Z3 AWG23 PRO4 CAT6A LSFRZH U/UTP XG SOLID** Part-no.: CS44Z3 C6A 4/23 U/UTP

Applied standard(s):

ISO/IEC 11801-1 Ed.1.0 (2017-11) IEC 61156-5 Ed.2.1 (2012-12)

Result(s):

The sample meets the limits of the applied standards and regulations with respect to the parameters indicated above.

Balanced cable, copper, Category 6^A GHMT PREMIUM Verification Program, GHMT PVP

Ongoing compliance with the specifications is monitored within the framework of regular sampling, which cannot be influenced by the customer, thus defining high standards as regards continuous manufacturing quality.

This Certificate refers to the comprehensive test report **no. R6210a-20** and shall only be applicable in conjunction with the test report.

Bexbach, 22.07.2020

Dirk Wilhelm, engineer (Chairman of the Managing Board)



Test laboratory accredited by DAkkS in accordance with DIN EN ISO/IEC 17025:2005.

The accreditation is valid for the test methods listed in certificate D-PL-17559-01-00.

66450 Bexbach / Germany

PO box11 16 66442 Bexbach / Germany

T: +49 6826 92 28-0 F: +49 6826 92 28-290

info@ghmt.de www.ghmt.de

GHMT AG

In der Kolling 320

RELIABILITY IN TOTAL REQUIRES ACCURACY IN DETAIL.

VALID TO NOVEMBER 2020

Category 6A