

FGSB-V9E44



FiberGuide® Vertical 90° 4in Inside Elbow Radius Limiter, Black

OBSOLETE

This product was discontinued on: October 1, 2023

Replaced By:

FGS-V9E44

FiberGuide® 4" deep 90° Inside Elbow, Yellow

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Accessory
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Angle/Bend Direction	90°
Color	Black
Orientation	Vertical
Section Type	Vertical section

Dimensions

Height	50.8 mm 2 in
Width	101.6 mm 4 in
Length	91.288 mm 3.594 in
System Dimensions	51 mm x 51 mm (2 in x 2 in)

Material Specifications

Material Type	Engineering Thermoplastic
----------------------	---------------------------

FGSB-V9E44

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Packaging and Weights

Included	Hardware
Packaging quantity	1
Weight, net	0.158 kg 0.348 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

