FGS-MSHS-H12



FiberGuide® Horizontal Straight Section, 4x24in, 12ft Length, Yellow

Product Classification

| Asia Australia/New Zealand EMEA Latin America North America | | |
|---|--|--|
| CommScope® | | |
| Straight section | | |
| FiberGuide® | | |
| FGS | | |
| | | |

General Specifications

| Product Feature | Slotted |
|-------------------|--------------------------------|
| Color | Yellow |
| Orientation | Horizontal |
| Section Type | Straight section |
| Dimensions | |
| Height | 102 mm 4.016 in |
| Width | 610 mm 24.016 in |
| Length | 3658 mm 144.016 in |
| System Dimensions | 102 mm x 610 mm (4 in x 24 in) |

Ordering Tree

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 5, 2024



FGS-MSHS-H12

yellow

black

6 ft

10 ft 12 ft



Section Color

Section Length

empty

9

11

Section Size

| Section Size | | |
|--------------|--------|---|
| 10 | А | 4 x 4 in |
| 10 | В | 4 x 6 in |
| | С | 2 x 2 in |
| | D | 4 x 4 in, slotted duct, 2 in slot spacing |
| | F | 4 x 12 in |
| | F-CF | 4 x 12 in, with center divider |
| | G | 2 x 6 in |
| | Н | 4 x 24 in |
| | К | 2 x 4 in, slotted duct, 2 in slot spacing |
| | STOR-B | 4 x 6 in, with slack storage spools |
| | STOR-G | 2 x 6 in, with slack storage spools |
| | STOR-F | 4 x 12 in, with slack storage spools |
| | | |

Material Specifications

Material Type

Engineering Thermoplastic

Environmental Specifications

| Flammability Rating | CSA S143 UL 2024 UL 94 V-0 |
|-------------------------|--------------------------------|
| Halogen Characteristics | Blue Angel TCO '99 WEEE |
| Safety Standard | CSA UL |

Packaging and Weights

| Packaging quantity | 2 |
|--------------------|----------------------|
| Weight, net | 5.953 kg 13.124 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 5, 2024



FGS-MSHS-H12



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 5, 2024

