

L2-PSMSM-HF

LDF2-50 Jumper with interface types SMA Male and SMA Male, variable length



Product Classification

Product Type	Wireless transmission cable assembly
Product Series	LDF2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	SMA Male
Interface, Connector B	SMA Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	3/8 in
---------------------	--------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
45–13000 MHz	1.577	13

Jumper Assembly Sample Label

L2-PSMSM-HF



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

- L2TSM-PL - SMA Male Positive Lock for 3/8 in LDF2-50 cable
- LDF2-50 - LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket