700006125 | D-181683



8-to-1 Unit Splitter, for outdoor cable diameter of 0.41 in

Product Classification

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America | | |
|-----------------------|---|--|--|
| Portfolio | SYSTIMAX® | | |
| Product Type | Unit splitter kit | | |
| Ordering Note | Order B sealant separately | | |

General Specifications

| Color | Black |
|----------------------|--------------------------|
| Compatible Interface | LC LC, keyed SC ST |

Dimensions

| Height | 11.176 mm 0.44 in |
|--------|---------------------|
| Width | 26.67 mm 1.05 in |
| Length | 68.58 mm 2.7 in |

Material Specifications

Material Type, body Acrylonitrile butadiene styrene (ABS)

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Packaging and Weights

Included Eight unit splitter | Split tube seal | Syringe

Packaging quantity

Regulatory Compliance/Certifications

1

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Page 1 of 1

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 4, 2023

