### FL1-P37777N2-0000C



FL1000 Fiber Wall Box, 2-door, singlemode SC/UPC, 72-ports, with adapters and pigtails (3mm x 3.5m), splice tray for heat shrink, 2 locks, key type A and B

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

#### **Product Classification**

Regional AvailabilityNorth AmericaProduct TypeFiber wall boxProduct SeriesFL1000

#### General Specifications

FunctionalityPatching| SplicingApplicationPatching| Splicing

Adapter Packs Included, quantity 8

Adapters, quantity 48

Cable Clamps, quantity 1

Cable Entry Location Bottom left | Bottom right | Top left | Top right

**Color** Putty white

Door, quantity 2

Front Door Type Single hinged
Growth Configuration Fully loaded
Interface SC/UPC

**Lock Type** Key lock, type A | Key lock, type B

**Mounting** Wall

**Splicing Type** Heat shrink, mass fusion

Total Fibers, quantity 48

Total Ports, quantity 48

**Dimensions** 

**COMMSCOPE®** 


## FL1-P37777N2-0000C

 Height
 708 mm | 27.874 in

 Width
 669 mm | 26.339 in

 Depth
 235.97 mm | 9.29 in

### Outline Drawing



#### Material Specifications

**Finish** Powder coated

Material Type Steel

Optical Specifications

**Fiber Mode** Singlemode

#### **Environmental Specifications**

Environmental Space Indoor

**Qualification Standards** NEMA type 12

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

**COMMSCOPE®** 

# FL1-P37777N2-0000C

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

