

FL1000 Fiber Wall Box, 2-door, empty box witout cable and adapters, no kits included

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification
------------------------

Regional Availability	North America
Product Type	Fiber wall box
Product Series	FL1000
General Specifications	
Functionality	Patching   Splicing
Application	Patching
Adapter Packs Included, quantity	2
Adapters, quantity	12
Cable Clamps, quantity	1
Cable Entry Location	Bottom left   Bottom right   Top left   Top right
Cable Type	IFC - Stranded
Color	Putty white
Door, quantity	2
Front Door Type	Single hinged
Growth Configuration	Fully loaded
Interface	SC/UPC
Lock Type	Key lock
Mounting	Wall
Total Fibers, quantity	12
Total Ports, quantity	12
Dimensions	
Usisht	100 mm   17.047 in

Height

433 mm | 17.047 in

Page 1 of 3


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024




# FL1-P

Width	511 mm   20.118 in
Depth	156.97 mm   6.18 in
Cable Length	229 m   751.312 ft

## Outline Drawing





Material Specifications
-------------------------

Finish	Powder coated
Material Type	Steel
Optical Specifications	
Fiber Mode	Singlemode

## Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA type 12
Packaging and Weights	
Packaging quantity	1
Packaging Type	Bag   Carton

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024



### Regulatory Compliance/Certifications

#### Agency

ROHS

#### Classification

CHINA-ROHS **REACH-SVHC** 

Below maximum concentration value Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

