

# 760239946 | 18" Pole Base 4G/5G, Round



Round 18 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low to mid power 4G/5G outdoor small cell site
- Base of 18in diameter accepts low power radios or mid-power dual band radios
- Concealment integrates AC load center/OVP and disconnect

## Product Classification

<b>Product Type</b>	Integrated pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, ANDREW</b>	ANDREW Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Compatible Smart Devices</b>	Cameras   Digital Signage   Emergency Call Station   Environmental Monitoring   Security Lighting   WIFI
<b>Cooling</b>	Fan Cooling
<b>Power Supply Compatibility</b>	ABB CC1600   DELTA 2.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	(3) 2205/2208 (Pole Top)   (6) 2203/2205/2208 radios   1281   220x   440x   4415   4426   4478   6701   6705   Diplexer   Power Distribution
<b>Radio Compatibility, Nokia</b>	(1) Airscale Dual Band 160W + (2) AirScale micro radios   (1) Airscale Dual Band 320W   (2) Airscale micro radios – LAA & CBRS (Pole Top)   (4) Airscale micro radios (Base)   AHFIA   AHIA   AHIB   AZRB   Diplexer   Power Distribution
<b>Radio Compatibility Samsung</b>	AT1K01   AT1K02   DELTA 2.0   Diplexer   Power Distribution   RF4402D-D1A   RT2201-46A   RT4401-48A

# 760239946 | 18" Pole Base 4G/5G, Round

---

**Radios Included** None

## Dimensions

**Height** 3,048 mm | 120 in

**Height Note** 10 ft tall Equipment Base

**Pole Height Options** 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

**Width** 457.2 mm | 18 in

**Depth** 457.2 mm | 18 in

**Depth Note** Round

**Pole Diameter** 203.2 mm | 8 in

## Electrical Specifications

**Power/Fiber Input** AC load center with OVP and disconnect

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Steel

## Environmental Specifications

**Thermal Compliance** GR-487