

CLT4HF-CO

Base Product



MQ Multiport cluster 4 ports cable assembly with interface type MQ female to 4.3-10 female, size 1/4"

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	MQ
Warranty	Two years

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	MQ Female
Interface, Connector B	4.3-10 Female
Specification Sheet Revision Level	A

Dimensions

Nominal Size	1/4 in
---------------------	--------

Port Configuration

Pin Assignment	Label
1	MQ4-1 (R-)
2	MQ4-2 (CR-)
3	MQ4-3 (CL-)
4	MQ4-4 (L-)

Mechanical Specifications

CLT4HF-CO

Minimum Bend Radius, multiple Bends 25.4 mm | 1 in

Minimum Bend Radius, single Bend 25.4 mm | 1 in

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Immersion Test Method IEC 60529, IP67

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines