

243684-M



Angle Adapter, compact, M10 tapped hole

Product Classification

Product Type	Adapter
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Adapter Type	Angle adapter
Mounting	M10 tapped hole

Dimensions

Inside Width	16.002 mm 0.63 in
Outside Width	38.1 mm 1.5 in
Inside Length	16.002 mm 0.63 in
Outside Length	46.99 mm 1.85 in
Material Thickness	2.972 mm 0.117 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Installation Torque, maximum	13 ft lb 17.626 N-m
Installation Torque, minimum	11 ft lb 14.914 N-m
Maximum Loading	Double stack, 1-5/8 in cable

Packaging and Weights

Height, packed	14 cm 5.512 in
Width, packed	14 cm 5.512 in
Length, packed	11 cm 4.331 in

243684-M

Packaging quantity 10
Weight, gross 1.59 kg | 3.505 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system