294562

ı



· c·

· ·

Snap-In Stand-off Adapter

Product Classification	
Product Type	Adapter
Product Brand	I-Line
Ordering Note	CommScope® non-standard product
General Specifications	
Adapter Type	Stand-off adapter
Mounting	3/4 in through hole
Dimensions	
Inside Width	44.45 mm 1.75 in
Outside Width	57.15 mm 2.25 in
Inside Length	60.452 mm 2.38 in
Outside Length	38.1 mm 1.5 in
Material Thickness	2.667 mm 0.105 in
Material Specifications	
Material Type	Stainless steel
Mechanical Specifications	
Installation Torque, maximum	15 ft lb 20.337 N-m
Installation Torque, minimum	11 ft lb 14.914 N-m
Maximum Loading	Double stack, 1-5/8 in cable

Packaging and Weights

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 22, 2024



294562

Packaging quantity	10
Weight, gross	1.7 kg 3.748 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 22, 2024

