

VSRC-TS-B



Interlocking Channel V-Stabilizer™ for Tower Legs 2-8in OD- Adjustable from 34.5" to 57.5" Plus Vertical & Horizontal Adjustments

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Pipe, quantity 0

Sectors, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

Length 1,460.5 mm | 57.5 in

Mounting Diameter, maximum 203.2 mm | 8 in

Mounting Diameter, minimum 50.8 mm | 2 in

Stand-off Distance, adjustable 34.5–57.5 in | 87.6–146 cm

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Legs

Packaging quantity 1

Weight, net 46.13 kg | 101.7 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

VSRC-TS-B

UK-ROHS

Compliant/Exempted

