9-552041-4 | INLINE MINI, BLUE, LP



Inline connector, 1000 loose piece, mini, blue

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates "turndowns"
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

Product Classification

Regional Availability

Australia/New Zealand | China | EMEA | Latin America | North America

Product Type Splice

General Specifications

Connector Color Code Blue

Connector Sealant Unfilled

Connector Splicing Type High Count Straight

Dimensions

Compatible Conductor Gauge, solid 26–22 AWG

Electrical Specifications

Safety Voltage Rating 400 Vdc

Material Specifications

Contact Base Material Phosphor Bronze

Contact Plating Material Tin

Insulation Material Air Core PIC | Paper or Pulp

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Environmental Space Outdoor

Packaging and Weights

Packaging quantity 1000

Page 1 of 2

9-552041-4 | INLINE MINI, BLUE, LP

Packaging Type Loose piece

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

