

RT-NF12-4-96



High Capacity Non-Penetrating Roof Frame, 12 ft face, four 2-7/8 in OD x 96 in pipes

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Pipe, quantity 4

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.81 m | 12.5 ft

Width 3,810 mm | 150 in

Length 2,377 m | 7.8 ft

Pipe Length 2,438.4 mm | 96 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Pipe Outer Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ballast tray | Frame | Plain end pipes (4)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

RT-NF12-4-96

REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

