## F4C-HMHM-4M-P



Product Classification

HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 4 m

• WARNING: DO NOT MATE WITH 4.1-9.5 DIN

PIUUULI LIASSIIILALIUII			
Product Type		SureFlex® Premiur	m, static PIM
Product Series		RSJ4-50	
General Specifications			
Body Style, Connector A		Straight	
Body Style, Connector B		Straight	
Interface, Connector A		4.3-10 Male	
Interface, Connector B		4.3-10 Male	
Specification Sheet Revision Level		В	
Dimensions			
Length		4 m   13.123 ft	
Nominal Size		1/2 in	
Electrical Specifications			
3rd Order IMD Static		-119 dBm	
3rd Order IMD Static Test Method		Two +43 dBm carri	ers per IEC 62037
DTF, Connector A		-34 dB	
DTF, Connector B		-34 dB	
VSWR/Return Loss			
Frequency Band	VSWR		Return Loss (dB)
698–960 MHz	1.065		30

1700-2200 MHz1.065302200-2700 MHz1.083283400-3800 MHz1.22220

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 16, 2022



## F4C-HMHM-4M-P

## Jumper Assembly Sample Label



## **Environmental Specifications**

**Immersion Test Method** 

Meets IEC 60529:2001, IP68 in mated condition

Page 2 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 16, 2022

