



Fiber Optic Pigtail, Simplex, Singlemode, SC/UPC to Stub, 0.9 mm diameter, 2 m, Kit of 100 pigtails

- Semi-tight cable stripping performance: 2 meter in steps of min. 30cm (in one operation). Applied force to remove each section is 10 N.

Product Classification

| | |
|------------------------------|-------------------------|
| Regional Availability | EMEA |
| Product Type | Fiber pigtail, jacketed |
| Product Series | OCP |

General Specifications

| | |
|-------------------------------|--------|
| Connector A, quantity | 1 |
| Color, boot A | Blue |
| Color, connector A | Blue |
| Interface, Connector A | SC/UPC |
| Jacket Color | Yellow |
| Total Fibers, quantity | 1 |

Dimensions

| | |
|--------------------|----------------|
| Cord Length | 2 m 6.562 ft |
|--------------------|----------------|

Ordering Tree

760253157 | OCP-S1-02MASEN-XX-(100)



| Connector/adaptor type | | |
|------------------------|------------------|------------|
| Standard C grade | Superior B grade | Type |
| S1 | SF | SC/UPC |
| S2 | SG | SC/APC 8° |
| S3 | SH | SC/APC 9° |
| L1 | LF | LC/UPC |
| L2 | LG | LC/APC |
| - | EC | LSH/APC 8° |

| Cable type | | | Fiber type |
|------------|--------|-------------------|------------|
| ASEN | 900 μm | Semi-tight jacket | A1 |
| HSEN | 900 μm | Semi-tight jacket | A2 |

| Cable length | |
|--------------|----------|
| 02 | 2 meters |

- Standard Configuration by default 900μm buffer
 buffer color : yellow
 250 μm color : natural or milky white

Optical Specifications

Fiber Mode Singlemode
Fiber Type G.657.A1, TeraSPEED®

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity 100

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

