


MC-PK10-C



Low-Profile Co-location Platform Kit, 10.5 ft face for 12 in to 50 in OD Monopoles, includes (12) 2 3/8" OD x 96" Antenna Pipes & Top Support Rail Kit

Product Classification

Product Type	Monopole platform kit
Ordering Note	NSTD445 Compliant

General Specifications

Mounting	Monopole, 304.8–1270 mm (12–50 in) OD
Pipe, quantity	12
Sectors, quantity	3

Dimensions

Height	2,438.4 mm 96 in
Face Width	3.2 m 10.5 ft
Platform Width	3,200.4 mm 126 in
Width	3,200.4 mm 126 in
Face Support Pipe Diameter	88.9 mm 3.5 in
Mounting Diameter, maximum	1,270 mm 50 in
Mounting Diameter, minimum	304.8 mm 12 in
Pipe Outer Diameter	60.325 mm 2.375 in
Stand-off Distance	914.4 mm 36 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

MC-PK10-C

Included	Plain end pipes (12) Platform Rail Ring mount
Packaging quantity	1
Weight, net	718.037 kg 1583 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--