UJVQXUCT8

Base Product



Ultra Low Loss (ULL) OM5 MPO8 (Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 8-Fiber, Dual Rated (OFNR/LSZH)

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity 1

Color, boot A Gray

Color, connector A Lime green

Connector B, quantity 0

Construction Type Stranded
Furcation Color Lime green

Interface, Connector A MPO-08/UPC Male

Interface, Connector BUnterminatedJacket ColorLime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 8

Dimensions

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305

Page 1 of 3




UJVQXUCT8

Cable Assembly Length Range (ft)

10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency Classification ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

760248170 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 8 fiber with 2.0

Page 2 of 3

UJVQXUCT8

N-008-MP-5G-F08LM/20T/D 860659020 mm subunits, Multimode OM5, Feet jacket marking, Lime-green jacket color, Dca flame rating MPO-08, ULTRA LOW LOSS, MALE, OM5, LIME-GREEN, 2mm

