

# RT-SF10-4-126

---



High Capacity Penetrating Roof Frame, 10 ft face, four 2-7/8 in OD x 126 in pipes

## Product Classification

**Product Type** Rooftop sector frame

## General Specifications

**Mounting** Penetrating

**Pipe, quantity** 4

## Dimensions

**Height** 3,200.4 mm | 126 in

**Face Width** 3.2 m | 10.5 ft

**Width** 3,200.4 mm | 126 in

**Length** 1.311 m | 4.3 ft

**Pipe Length** 3,200.4 mm | 126 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

**Pipe Outer Diameter** 73.152 mm | 2.88 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Frame | Plain end pipes