

760254378 | RMM-12UF-12UF-OM5-ULL



1RU rack mounted Multimode OM5 mesh module with all front facing MPO12 ports. 24, 12f inputs from separate network enclaves to 24, 12f outputs to the desktop with Ultra-Low Loss (ULL) performance

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber patch panel

General Specifications

Interface, front	MPO
Interface Feature, front	Shuttered Unpinned
Rack Units	1
Shelf Movement	Fixed
Total Fibers, quantity	288
Total Ports, quantity, front	48

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED®
Insertion Loss, maximum	0.4 dB

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

760254378 | RMM-12UF-12UF-0M5-ULL

ROHS

Compliant

UK-ROHS

Compliant

