

760254379 | RMM-12UR-12UF-OM5-ULL



1RU rack mounted Multimode OM5 mesh module with 24, MPO12 inputs on the back from separate network enclaves and 24, MPO12 outputs to the desk top on the front with Ultra-Low Loss (ULL) performance

Product Classification

Regional Availability	Asia EMEA North America
Portfolio	CommScope®
Product Type	Fiber patch panel

General Specifications

Interface, front	MPO
Interface Feature, front	Shuttered Unpinned
Interface, rear	MPO
Interface Feature, rear	Shuttered Unpinned
Rack Units	1
Shelf Movement	Fixed
Total Fibers, quantity	288
Total Ports, quantity	48
Total Ports, quantity, front	24

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5, LazrSPEED®
Insertion Loss, maximum	0.4 dB

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

760254379 | RMM-12UR-12UF-0M5-ULL

Agency

CHINA-ROHS
ISO 9001:2015
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant
Compliant/Exempted

