

CLT4MQ-CO

Base Product



MQ Multiport cluster 4 ports cable assembly with interface type MQ female to MQ female, size 1/4"

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	MQ
Warranty	Two years

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	MQ Female
Interface, Connector B	MQ Female
Specification Sheet Revision Level	A

Dimensions

Nominal Size	1/4 in
---------------------	--------

Port Configuration

Pin Assignment	Label
1	MQ4-1 (R-)
2	MQ4-2 (CR-)
3	MQ4-3 (CL-)
4	MQ4-4 (L-)

VSWR/Return Loss

CLT4MQ-CO

Frequency Band	VSWR	Return Loss (dB)
0–2700 MHz	1.151	23.1
2700–4200 MHz	1.201	20.8
4200–6000 MHz	1.352	16.5

Mechanical Specifications

Minimum Bend Radius, multiple Bends	25.4 mm 1 in
Minimum Bend Radius, single Bend	25.4 mm 1 in

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Immersion Test Method	IEC 60529, IP67

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines