## FST-HD-RR



Fiber Optic Splice Tray, 432 Rollable Ribbon Splice Capacity

## Product Classification

Regional Availability	Latin America   North America
Product Type	Fiber splice tray
Product Series	FEC

## General Specifications

Application	For use in FEC splice cabinet
Color	Black
Splicing Capacity, maximum	432
Splicing Type	Mass fusion, ribbon
Dimensions	
Height	23.368 mm   0.92 in
Width	131.572 mm   5.18 in

width	131.37211111   3.10111
Length	298.45 mm   11.75 in

## Environmental Specifications

Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Space	Indoor

Page 1 of 1

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: August 16, 2022

