MC-DPM3-126



Monopole Co-location Dual Pipe Mount Kit, 4 ft 9 in face, includes pipe

Product Classification

Product Type Co-location dual pipe mount kit

General Specifications

Pipe, quantity 2
Sectors, quantity 1

Dimensions

Stand-off Distance

Height 3,200.4 mm | 126 in

 $\textbf{Face Width} \hspace{1.5cm} 1.463\, m \hspace{0.2cm} | \hspace{0.2cm} 4.8 \hspace{0.2cm} ft$

 Width
 1,447.8 mm | 57 in

 Length
 355.6 mm | 14 in

 Pipe Length
 3,200.4 mm | 126 in

 Pipe Outer Diameter
 73.66 mm | 2.9 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Criteria Four 72 in x 8 in panel antennas per sector

355.6 mm | 14 in

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Dual pipe frames | Pipe mounts

Packaging quantity 1

Weight, net 102.104 kg | 225.1 lb

ANDREW®
an Amphenol company

MC-DPM3-126

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

