

# SSH-411

---



SnapTak PIM-Guard® Adjustable Hanger, Gen 2. Fits 4.0 mm to 11.0 mm Cables – PIM Free Polymer Construction. No Grommets Required

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	SnapTak PIM-Guard®
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Accessories</b>	Hangers
<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in drilled cable ladder

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Maximum Stack Height, Coaxial</b>	3
<b>Height</b>	42.8 mm   1.685 in
<b>Width</b>	32 mm   1.26 in
<b>Length</b>	46.7 mm   1.839 in
<b>Compatible Cable Diameter Range</b>	4–11 mm
<b>Compatible Diameter, maximum</b>	11 mm   0.433 in
<b>Compatible Diameter, minimum</b>	4 mm   0.157 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

# SSH-411

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥1000 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 3.1 cm | 1.22 in

**Width, packed** 20.3 cm | 7.992 in

**Length, packed** 25.4 cm | 10 in

**Packaging quantity** 10

**Weight, gross** 0.36 kg | 0.794 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power