

A7818479 | Optical Demultiplexer, 18 channels



CWDM Fiber Optical Module, Demux, 1270-1610 nm, LC/PC, 18 channels

- Trade Agreements Act (TAA) compliant

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | CWDM module |
| Product Series | LGX |

General Specifications

| | |
|----------------------|----------------|
| Functionality | Demultiplexing |
|----------------------|----------------|

Dimensions

| | |
|---------------|--------------------|
| Height | 44 mm 1.732 in |
| Width | 483 mm 19.016 in |
| Depth | 290 mm 11.417 in |

Packaging and Weights

| | |
|-----------------------|--------------------|
| Height, packed | 90 mm 3.543 in |
| Width, packed | 548 mm 21.575 in |
| Depth, packed | 345 mm 13.583 in |
| Weight, gross | 2.1 kg 4.63 lb |
| Weight, net | 1.7 kg 3.748 lb |