



Wall-mountable Optic fiber outlet with 3 LC/APC shuttered Duplex adapters and no pigtails, for ANT splice protection

- Laser safe with in-built individual shutters
- Can be used for entering with a blown fiber tube and storing the Gasblock
- Satellite wall outlet possibility for a second living unit
- Safety cap on drop ports against easy removal

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber wall outlet
Minimum Order Quantity	10

General Specifications

Color	White
Distribution Type	6 ports
Mounting	Wall mount
Patching Capacity, maximum	6
Pigtails Included, quantity	1

Dimensions

Height	120 mm 4.724 in
Width	105 mm 4.134 in
Depth	34 mm 1.339 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Performance Grade	Standard C grade

Environmental Specifications

Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
----------------------------	--------------------------------------

Environmental Space Indoor

Flammability Rating UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

