## CB9644-000 | OCJ-L1-10MASIA-S1



Fiber Optic Patch Cord, Simplex, Singlemode, LC/UPC to SC/UPC, yellow, 10 m

### Product Classification

Regional Availability	EMEA
Product Type	Fiber patch cord, simplex
Product Series	OCJ
General Specifications	
Connector A, quantity	1
Color, boot A	Blue
Color, connector A	Blue
Connector B, quantity	1
Color, boot B	Blue
Color, connector B	Blue
Interface, Connector A	LC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1
Dimensions	
Cable Assembly Length Range (m)	1 – 999
Cable Assembly Length Range (ft)	1 – 999
Cord Length	10 m   32.808 ft
Diameter Over Jacket	1.8 mm   0.071 in

## Ordering Tree

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2023



## CB9644-000 | OCJ-L1-10MASIA-S1

## 

Connector type at end 1		
Standard C grade	Superior B grade	Туре
S1	SF	SC/UPC
S2	SG	SC/APC 8°
S3	SH	SC/APC 9°
L1	LF	LC/UPC
L2	LG	LC/APC
-	EC	LSH/APC 8°

Standard C grade	Superior B grade	Туре
S1	SF	SC/UF
S2	SG	SC/APC

51	51	56,616
S2	SG	SC/APC 8°
S3		SC/APC 9°
L1	LF	LC/UPC
L2	LG	LC/APC
-	FC	I SH/APC 8°

<sup>1</sup> For hybrid patch cords, connectors 1 and 2 must be the same grade.

Connector type at end 2<sup>1</sup>

(	Ca
	1

	Cable typ	De	
_	ASIA	1.8mm simplex	LSZH jacket
	ASHA	1.8mm duplex	LSZH jacket

## **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	G.657.A1, TeraSPEED®
Performance Grade	Standard C grade
Insertion Loss, maximum, connector A	0.5 dB
Insertion Loss, maximum, connector B	0.5 dB
Return Loss, minimum, connector A	50 dB
Return Loss, minimum, connector B	50 dB

#### **Environmental Specifications**

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)
Dackaging and Moights	

#### Packaging and Weights

Packaging quantity

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2023

1



# CB9644-000 | OCJ-L1-10MASIA-S1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



×E

### \* Footnotes

**Performance Grade** Guarantee to meet IEC 61755-1 Random Mating requirement

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 16, 2023

