UGGRXUCYR



Hybrid Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Pinned) to Unconnectorized, 2 Pair 16AWG Constellation Trunk Cable Assembly, 16-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product TypeHybrid cable assembly | 2-pair

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Conductor Capacitance 75.459 pF/m | 23 pF/ft

Conductor Resistance 14.698 ohms/km | 4.48 ohms/kft

Conductor Type 16 AWG | Stranded

Conductors, quantity 4
Conductor Pairs, quantity 2
Connector A, quantity 1

Color, boot ABlackColor, connector AGreen

Construction TypeHybrid standard trunk

Furcation Color Yellow

Interface, Connector A MPO-16/APC Male

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 16

Total Fibers, quantity 16

Dimensions

Breakout Length 24 in | 72 in


COMMSC PE°

UGGRXUCYR


Cable Assembly Length Range (m) 10 – 999

Cable Assembly Length Range (ft) 33 - 999

Dimension Drawing



Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®



UGGRXUCYR

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (+14 °F to } +140 \,^{\circ}\text{F)}$

Environmental SpaceIndoorPlenumQualification StandardsGR-3108 class 4

Included Products

860661398 – Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm

cable



860661398



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connector

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface Feature Pinned

Dimensions

Compatible Cable Diameter 3 mm | 0.118 in

Optical Specifications

Fiber Mode Singlemode

Fiber TypeOS2Insertion Loss, maximum0.3 dBReturn Loss, minimum65 dB

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 4 of 5

860661398

ROHS

Compliant Compliant

UK-ROHS



