

# MUK-SFK3 | V-BRACING KIT

---



V-Stabilizer for Tower with saddle clamps for 1.5" - 8" Tower legs, Dual Pivoting Angle Arms, 96" long, attaches up to 4-1/2" OD horizontals

## Product Classification

**Product Type** Reinforcement kit

## General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Round member | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 0

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Mounting Diameter 2, maximum** 114.3 mm | 4.5 in

**Mounting Diameter, maximum** 203.2 mm | 8 in

**Mounting Diameter, minimum** 38.1 mm | 1.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamps | Legs | Saddle mount

**Packaging quantity** 1