

7844068-02 | WCS-4 DC



ERA® Wireless Communications Switch Subrack, 4 U -48Vdc, with integrated DCDC converter

This unit does not support CAT6A powered access points.

Product Classification

Product Type Subrack

Product Brand ERA®

General Specifications

Mounting Rack

Note Detailed Product Specifications are available. Please contact your local ANDREW representative.

Rack Type EIA 19 in

Slots Available, quantity 19

Dimensions

Height 177 mm | 6.969 in

Width 482 mm | 18.976 in

Depth 450 mm | 17.717 in

Packaging and Weights

Height, packed 540 mm | 21.26 in

Width, packed 600 mm | 23.622 in

Depth, packed 290 mm | 11.417 in

Included Fan filter | Fan tray

Weight, gross 15.8 kg | 34.833 lb

Weight, net 13.4 kg | 29.542 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

