HFTP-NO



HFTP Customer premises fiber wall outlet

Ideal for FTTH and FTTB applications, the HFTP is a compact fiber terminal for use at the final fiber termination point in the customer premises. The HFTP provides mechanical protection and managed fiber control in an attractive format suitable for use inside customer premises.Complete kits are available which include CommScope connectors, mechanical splices and cable assemblies for all installation options.

A variety of possible fiber termination techniques are accommodated

- Splicing to factory terminated pigtails
- Direct termination with field installable connectors.

Features:

- Attractive design options for indoor use
- Managed fiber control
- Mechanical or fusion splicing
- Direct termination
- Splice cable to cable
- Compatible with SC or duplex LC adaptors
- Multiple cable entry points (cable diameter≤6mm)

Product Classification

EMEA Regional Availability

Product Type Fiber wall outlet

Product Series HFTP

Minimum Order Quantity 300

General Specifications

Color White **Cover Type**

Interface Type LC/APC | LC/UPC | SC/APC | SC/UPC | Unloaded

Screw-on

Page 1 of 3



HFTP-NO

Mounting Wall mount


Dimensions


 Height
 105.41 mm | 4.15 in

 Width
 82.55 mm | 3.25 in

 Depth
 23.876 mm | 0.94 in


Outline Drawing





Ordering Tree

HFTP-NO



Material Specifications

Material Type LSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Relative Humidity Up to 93%, non-condensing

Environmental Space Indoor

Packaging and Weights

Packaging quantity 10