	4	3	
D	<ol> <li>1.0 GENERAL NOTES         <ol> <li>ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]</li> <li>FOR PATENT INFO: <a href="https://www.cs-pat.com">https://www.cs-pat.com</a></li> </ol> </li> <li>2.0 DESIGN NOTES         <ol> <li>KIT WILL WORK WITH 12 FOOT MC-PM4 PLATFORM KITS AND MONOP</li> <li>MANUFACTURING/SPECIAL REQUIREMENTS</li> <li>TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT I USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DI EACH LEG OF THE U-BOLT.</li> </ol> </li> <li>TEST</li> <li>PACKAGING         <ol> <li>PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUM 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN \$             <li>SATRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED</li> </li></ol> </li> </ol>	OLE SIZES FROM 15" OD TO 45" OD. METHOD. TIGHTEN ALL U-BOLTS ISTANCE AND EQUAL FORCE ON IENT IS-PL-3005	(1)
			2
С			3
В			
5			AX 150.00 13810.01
		250 6350 1118	
A	COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPO		
	ITEM PART NO. DESCRIPTION	QTY. WEIGHT NOTE NO.	SUI

	INDIVIDUAL COMPONENTS MAT BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.					
	ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT	NOTE N
-	1	MC4-HR25X-2000	CORNER WELDMENT SNUB NOSE HANDRAIL	4	34.72 LBS	
	2	GUB-4352	1/2" X 3" X 5-1/4" GALV U-BOLT	16	0.71 LBS	
	3	MT-546-150	PIPE, 2.875"OD X 150"	4	72.67 LBS	
	-					


C 2022 CommScope, Inc. Confidential

3

 $\square$ 

4


		I				
	REVISIONS					
	REV.	DESCRIPTION	DATE	APPROVED		
	А	INITIAL RELEASE	YMENG 21OCT21	BA1025 15811		
	В	UPDATED VIEW ON SHEET 2 TO MATCH PLATFORM CHANGED	YMENG 08OCT22	BA1025 40156827CMO		




В

С

D



2



 $\square$ 

С

-

В

А