





NOTES:

- 1.0 GENERAL NOTES
- 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS.
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
- 4.0 TEST
- 5.0 PACKAGING

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	8000034283	INITIAL RELEASE	RJC	03/08/19
B	8000034962	ECN WAS CLOSED OUT AND NEVER RELEASED	RJC	06/15/19
C	8000036883	UPDATED TABLE MT-546-174 WAS MT-546-170	RJC	08/22/19



ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
1	MT19525	CORNER WELDMENT FOR MT-195	3	16.89 LBS	
2	GUB-4240	1/2" X 2-1/2" X 4" GALV U-BOLT	12	0.56 LBS	
3	GUB-4352	1/2" X 3" X 5-1/4" GALV U-BOLT	24	0.71 LBS	
4	XAU01	ANGLE, CROSSOVER, 1.9-3.5" X 1.9-3.5" OD	12	2.98 LBS	
5	MT-546-150	2-7/8" OD x 150" GALV PIPE	3	72.67 LBS	SEE TABLE FOR PIPE

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE X ± .25	2 PLACE .XX ± 0.06	MT-195-HD	
1 PLACE .X ± 0.12	ANGLES ± 2°		
FINISH GALV A123		MATERIAL A500, A1011/A1018	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	NAME	DATE	TITLE
	CE RJC	03/08/19	HANDRAIL KIT, HD, MONOPOLE PLTFM SERIES
	RW BCAMPBELLCON	08/22/2019	
	RV MC1107	08/22/2019	
AD FA1024	08/27/2019		
RE	ECN 008000034283	SCALE	DOCUMENT NO.
		1:20	MT-195-HD
SIZE	WORK AREA 24	MODEL	
C		VERSION	STATUS
		00	RE
		DRAWING	
		VERSION	STATUS
		00	RE
		REVISION	REVISION
		C	C
			SHEET
			1 OF 1

PART NUMBER	PIPE	DESCRIPTION	WEIGHT
MT-195-8HD	MT54696	HANDRAIL KIT, 8' FACE, HD, MONOPOLE PLTFM	262.00 LBS
MT-195-10HD	MT-546-126	HANDRAIL KIT, 10' FACE, HD, MONOPOLE PLTFM	298.32 LBS
MT-195-12HD	MT-546-150	HANDRAIL KIT, 12' FACE, HD, MONOPOLE PLTFM	326.63 LBS
MT-195-14HD	MT-546-174	HANDRAIL KIT, 14' FACE, HD, MONOPOLE PLTFM	358.80 LBS

DENSITY	0.28	lbs/in ³
MASS	334.83	lbs
VOLUME	1303.29	in ³
SURFACE AREA		in ²
HEIGHT	12.0	
LENGTH	174	
WIDTH	12.0	

