## PM-SU4-63



#### Universal Sliding Pipe Mount Kit for 4-1/2 in OD x 63 in pipe

#### **Product Classification**

Product Type Pipe mount

#### General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

**Note** One 96 in x 8 in panel antenna per sector

Pipe, quantity 1

**Tower Taper** Tapered

#### Dimensions

 Height
 1,600.2 mm | 63 in

 Width
 304.8 mm | 12 in

 Length
 304.8 mm | 12 in

 Pipe Length
 1,600.2 mm | 63 in


 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 0 mm | 0 in

Pipe Outer Diameter 114.3 mm | 4.5 in



## Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

## Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL

Wind Rating Test Method TIA/EIA-222

#### Packaging and Weights

Included Pipe | Sliding pipe mount brackets | Universal saddle mount

Packaging quantity 1

ANDREW® an Amphenol company

## PM-SU4-63

**Weight, net** 62.6 kg | 138.009 lb

#### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

MT-653-63 – Plain End Pipe, 4-1/2 in OD x 63 in x .237" A500C 46Ksi

PM-SL4 – Universal Taper Pipe Mount Slider Bracket for 4-1/2 in OD pipe

SM-U2080 – Universal Saddle Mount for straight or tapered legs up to 8 in OD, 8 in angle 60°, or 6 in angle

90° (Kit of 2)

#### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



## MT-653-63



#### Plain End Pipe, 4-1/2 in OD x 63 in x .237" A500C 46Ksi

#### **Product Classification**

Product Type Plain end pipe

#### General Specifications

Pipe, quantity 1

#### **Dimensions**

 Height
 114.3 mm | 4.5 in

 Width
 114.3 mm | 4.5 in

 Length
 1,600.2 mm | 63 in

 Pipe Length
 1,600.2 mm | 63 in

 Pipe Outer Diameter
 114.3 mm | 4.5 in

 Material Thickness
 6.02 mm | 0.237 in

#### Material Specifications

Material Type A500 | Hot dip galvanized steel

Material Grade C

Material Strength 46 KSI

#### Packaging and Weights

**Included** Pipe **Packaging quantity** 1

**Weight, net** 25.9 kg | 57.1 lb

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



## PM-SL4



#### Universal Taper Pipe Mount Slider Bracket for 4-1/2 in OD pipe

#### **Product Classification**

Product Type Pipe mount

#### General Specifications

**Mounting** Saddle mounts

**Note** One 96 in x 8 in panel antenna per pipe mount

Pipe, quantity 0

**Tower Taper** Tapered

#### **Dimensions**

 Height
 127 mm | 5 in


 Width
 152.4 mm | 6 in

 Length
 304.8 mm | 12 in

 Pipe Outer Diameter
 114.3 mm | 4.5 in

## PM-SL4

#### Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

## Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL

Wind Rating Test Method TIA/EIA-222

#### Packaging and Weights

Included Hardware | Sliding pipe mount brackets

Packaging quantity 2



## PM-SL4

**Weight, net** 14.2 kg | 31.306 lb

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

\* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



#### SM-U2080



Universal Saddle Mount for straight or tapered legs up to 8 in OD, 8 in angle 60°, or 6 in angle 90° (Kit of 2)

#### **Product Classification**

**Product Type** Saddle mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

**Tower Taper** Non-tapered

**Dimensions** 

 Height
 152.4 mm | 6 in

 Width
 279.4 mm | 11 in

 Length
 254 mm | 10 in

 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 0 mm | 0 in

Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

**Included** Mount

Packaging quantity 2

**Weight, net** 22.7 kg | 50.045 lb

#### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

Page 8 of 9



# SM-U2080

