

# RF-NL10-4-96

---



Non-Penetrating Roof Frame, 10 ft face, Four 3-1/2 in OD x 96 in pipes

## Product Classification

**Product Type** Non-penetrating roof frame

## General Specifications

**Mounting** Non-penetrating  
**Note** Four 96 in x 18 in panel antennas per sector  
**Pipe, quantity** 4

## Dimensions

**Height** 2,438.4 mm | 96 in  
**Face Width** 3.2 m | 10.5 ft  
**Width** 3,200.4 mm | 126 in  
**Length** 2.53 m | 8.3 ft  
**Pipe Length** 2,438.4 mm | 96 in  
**Pipe Outer Diameter** 88.9 mm | 3.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479  
**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Rubber mats, with or without pipe mounts

# RF-NL10-4-96

---

**Packaging quantity** 1  
**Weight, net** 309 kg | 681.228 lb

\* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code