



any pigtails and/or adapters are not shown in the image



HFTP-AM Customer premises fiber wall outlet, no pigtails, no adapter, with the capacity to store for 4 splices

- Compact fiber wall outlet for use at the final fiber termination point in the customer premises
- Can be wall mounted and mounted on wall boxes with fixation points of 60mm
- Direct termination with field installable connectors
- Laser safe with in-built individual shutters

Product Classification

Product Type	Fiber wall outlet
Product Series	HFTP
Minimum Order Quantity	75

General Specifications

Color	White
Cover Type	Screw-on
Mounting	Wall mount
Pigtails Included, quantity	0
Total Ports, quantity	1

Dimensions

Height	104.902 mm 4.13 in
Width	84.836 mm 3.34 in
Depth	24.892 mm 0.98 in

Material Specifications

Material Type	LSZH thermoplastic
----------------------	--------------------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing

760256175 | HFTP-AM-LN00-E

Environmental Space Indoor

Packaging and Weights

Packaging quantity 75