

# TF-ML4-8



Tower Face Mount with dual 8 ft x 4-1/2 in OD face pipe supports, includes pipe

## Product Classification

**Product Type** Tower face mount

## General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 1

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 96 in | 2,438.4 mm

**Face Width** 8 ft | 2.438 m

**Width** 96 in | 2,438.4 mm

**Length** 12 in | 304.8 mm

**Pipe Length** 96 in | 2,438.4 mm

**Face Support Pipe Diameter** 4.5 in | 114.3 mm

**Mounting Diameter, maximum** 8 in | 203.2 mm

**Mounting Diameter, minimum** 0 in | 0 mm

**Pipe Outer Diameter** 4.5 in | 114.3 mm

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

# TF-ML4-8

---

<b>Included</b>	Crossover plates   Pipes   Saddle mounts
<b>Packaging quantity</b>	1
<b>Weight, net</b>	576.9 lb   261.677 kg

## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--