


300100113592 | FD3-AC144J00WBBP2-B



FDH 3000 Fiber Distribution Extra Small Cabinet, 144F, SC/APC, no splitters, Arm. Ribbon, 100 ft, 24FF

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Armored - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole
Splitter Slots, quantity	9

Dimensions

Height	914.4 mm 36 in
Width	533.4 mm 21 in
Depth	355.6 mm 14 in
Cable Length	30.48 m 100 ft
Enclosure Size	Extra small

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

