

1100-DM-PANELS



SYSTIMAX 1100 Series Distribution Module Panels

Product Classification

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

General Specifications

Color

Black

Rack Type

EIA 19 in

Electrical Specifications

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,000 Vac @ 60 Hz | 1,500 Vac @ 60 Hz

Mechanical Specifications

Plug Insertion Life, test plug

IEC 60603-7 compliant plug

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity

Up to 95%, non-condensing

Flammability Rating

UL 94 V-0

Safety Standard

UL | cUL