CSC1-U8C1ABBCOOO



NOVUX™ CSC40 Compact Fiber Closure, splice/patch, XpressDrop 4 SC /APC adapters, no pigtails, 1x4 splitter connectorised input/output, mounting bracket, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability Asia

Portfolio CommScope®

Product Type Single-ended, rectangular fiber closure

Product Brand NOVUX™

Product Series CSC 40

Minimum Order Quantity 6

General Specifications

Cable Ports Quantity, total 2 round ports + 4 multi-out ports (8 cables)

Cable Sealing TypeCompressed gelClosure Sealing TypeHinged with latchClosure StyleSingle-ended

Color Black

Mounting Pole | Wall

Port Type SC/APC

Port, quantity 4

Splicing Capacity, maximum 48

Splitter Type 1 x 4

Splitter, quantity 1

COMMSCOPE®

CSC1-U8C1ABBC000

Dimensions

 Height
 215 mm | 8.465 in

 Width
 117 mm | 4.606 in

 Depth
 77 mm | 3.031 in

 Length
 215 mm | 8.465 in

Environmental Specifications

Environmental Space Outdoor

UV Resistance UV stabilized

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Packaging Type Box | Carton