# 760250963 | CMC-74-36B



#### CMC-74, NiCd Battery Cabinet 6-String, with 1 kW Heater

The cabinet is designed to accommodate 6 strings of -48V NiCad batteries into one cabinet. This cabinet provides mechanical and environmental protection for the equipment inside. The standard cabinet provides a 1000W heater on front door.

- Excellent thermal performance to ensure the battery could be applied in harsh environments.
- Provides option for security/access control via Puck Lock system.
- Provides flexible access for the cable entrance.
- Provides flexible heater solution for the cold ambient application.
- · Product platform shares many parts including plinth, solar shield, and hybridcable storage units.
- · Excellent cable management system.

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Macro cell site enclosure

Product Series CMC

## General Specifications

Access Bottom: Power compartment | Rear Wall: Hybrid Cables | Side Wall: Power or other cables

compartment | Top Roof: Alternative Hybrid Cable entrance

Alarm Type Door open (both front and side doors) | HVAC alarms (including high temperature,

failure) | Overheat | S2 module, 20P or standard and user defined alarms | Thermal probe

**Batteries** Not included

**Batteries Supported** 6 strings of NiCad batteries from Multiple OEM (not supplied by CommScope)

**Battery Storage** 4 battery shelves for holding up to 6 Nicad battery strings

Capacity 1000 W Heater

Color Light Gray (RAL 7035) | Others available at additional cost

**Door Security**Quarter turn lock, puck lock system for rear door | Swing handle, puck lock system for front door

**Grounding Connection** 12 positions

Mounts directly to steel dunnage with supplied ½" hardware | Mounts to concrete pad with customer

supplied anchors | Optional 6" plinth

**Noise Emission, maximum** 60 dBA

Dimensions



# 760250963 | CMC-74-36B


939.8 mm | 37 in

 Height
 1,879.6 mm | 74 in

 Width
 914.4 mm | 36 in

## Dimension Drawing

Depth



# **Electrical Specifications**

Alarm Output Dry contacts

### Cabinet Mounting



# 760250963 | CMC-74-36B

## Material Specifications

Finish Powder coated | UV resistant

Material Type Aluminum

# **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+46 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +115  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Qualification Standards ANSI/UL 62638-1 | ETL 4007237 | GR-487 | IEC 60529, IP55 | Seismic rating, zone 4 | UL

1801

#### Packaging and Weights

**Weight, net** 462.211 kg | 1019 lb

