

# 760235092 | M2400-1U-GS-VCM



M2400 1U Modular Panel for 12" VCM, 24 port (MGS600 / MGS400 / UNJ10GT), Black

- Panel is designed to fit the VCM 12" (Vertical Cable Management Kit, 12inch ) portfolio

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	RJ45 patch panel
<b>Product Brand</b>	GigaSPEED X10D®
<b>Product Series</b>	M Series

## General Specifications

<b>ANSI/TIA Category</b>	6   6A
<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Intelligence Type</b>	Passive
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	0
<b>Total Ports, quantity</b>	24

## Dimensions

<b>Height</b>	43.69 mm   1.72 in
<b>Width</b>	279.45 mm   11.002 in
<b>Depth</b>	53.59 mm   2.11 in
<b>Compatible Diameter Over Dielectric, maximum</b>	1.168 mm   0.046 in
<b>Compatible Diameter Over Dielectric, minimum</b>	0.762 mm   0.03 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---