

# F1A-XMHM-6M-P



FSJ1-50A SureFlex® Jumper with interface types NEX10 Male and 4.3-10 Male, 6m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	SureFlex® Premium, static PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	FSJ1-50A

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	NEX10 Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	6 m   19.685 ft
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>3rd Order IMD</b>	-116 dBm
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–970 MHz	1.065	30
1700–2200 MHz	1.083	28
2200–2700 MHz	1.106	26
3400–3800 MHz	1.222	20

## Jumper Assembly Sample Label

# F1A-XMHM-6M-P

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition