1-1920743-1



Fiber Optic Patch Cord, LC to LC, duplex, OM3 XG 10 Gb/s, twin zip, 11 m, aqua

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | India

Portfolio CommScope®

Product Type Fiber patch cord, duplex

Product Series 192

General Specifications

Connector A, quantity 2

Color, boot ABeigeColor, connector ABeige

Connector B, quantity 2

 Color, boot B
 Beige

 Color, connector B
 Beige

 Interface, Connector A
 LC/UPC

 Interface, Connector B
 LC/UPC

Jacket Color Aqua

Total Fibers, quantity 2

Dimensions


 Cord Length
 11 m | 36.089 ft

 Diameter Over Jacket
 1.8 mm | 0.071 in

Ordering Tree



1-1920743-1



Optical Specifications

Fiber Mode Multimode

Fiber Type OM3, LazrSPEED®

Insertion Loss, maximum, connector A 0.15 dB
Insertion Loss, maximum, connector B 0.15 dB
Return Loss, minimum, connector A 35 dB
Return Loss, minimum, connector B 35 dB

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

COMMSCOPE®

1-1920743-1





