

Fiber Optic Patch Cord, Simplex, 0.9mm, LSZH, Singlemode, LC/UPC to LC/UPC, Yellow, 4 m

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | India

Yellow

Portfolio CommScope®

Product Type Fiber patch cord, simplex

Product Series 210

General Specifications

Connector A, quantity

Color, boot A Blue
Color, connector A Blue

Connector B, quantity 1

Color, boot BBlueColor, connector BBlue

Interface, Connector ALC/UPCInterface, Connector BLC/UPC

Total Fibers, quantity 1

Dimensions

Jacket Color


Cord Length 4 m | 13.123 ft

Diameter Over Jacket 0.9 mm | 0.035 in

Ordering Tree



2105081-4



Mechanical Specifications

Cable Retention Strength, maximum $1.00 \text{ lb} @ 0 \degree | 1.00 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1, TeraSPEED®

 Insertion Loss, maximum
 0.25 dB

 Return Loss, minimum
 50 dB

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



COMMSCOPE®