

MC-PM12M4-B

Atlas 4-Sector Monopole Platform Base kit, 15 in to 45 in OD, 2-7/8 in OD x 12 ft 6 in face. Top rail & antenna pipe/mounts ordered separately.



Product Classification

Product Type	Monopole platform kit
Product Series	ATLAS

General Specifications

Pipe, quantity	0
Sectors, quantity	4

Dimensions

Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	1,143 mm 45 in
Mounting Diameter, minimum	381 mm 15 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Platform Ring mount
Packaging quantity	1

MC-PM12M4-B

Weight, net 1,233.091 kg | 2,718.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code