760254717 | PPL-AP-6-MPO-ALL-A



Propel pass-through adapter pack, 6 MPO8-12-24 ports, Type A

- Can be installed and removed from front or rear of panel
- For use with MP08, MP012 or MP024 applications
- All adapter pack sizes are interchangeable within Propel panels or blades
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America		
Portfolio	SYSTIMAX®		
Product Type	Fiber adapter pack		
Product Brand	Propel		
Product Series	PPL		

General Specifications

Adapter Color	Black
Interface	MPO
Interface Feature	Dust caps Internal shutters Key down
Total Ports, guantity	6

Dimensions

Height	11 mm 0.433 in
Width	98 mm 3.858 in
Depth	170 mm 6.693 in

Optical Specifications

Fiber Mode	Multimode	Singlemode
------------	-----------	------------

Environmental Specifications

Safety Standard

c-UL-us

1

Packaging and Weights

Packaging quantity

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 23, 2024



760254717 | PPL-AP-6-MPO-ALL-A

Regulatory Compliance/Certifications

Agency

ROHS

Classification

CHINA-ROHS **REACH-SVHC**

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant



UK-ROHS

Compliant

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 23, 2024

