

MFT-G24-AA-JA



HELIAX® Modular Fiber Cable, assembly, 24 single mode fibers, End 1: DLC GEN1.5; End 2: DLC GEN 1.5; LSZH cable. Anti-rodent with E-Glass Protection.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®

General Specifications

Interface, Connector A	DLC GEN 1.5
Interface Feature, connector A	Standard
Interface Body Style, connector A	Straight
Interface, Connector B	DLC GEN 1.5
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	24

Dimensions

Cable Assembly Length Range (m)	1 – 15
Diameter Over Jacket	8.9 mm 0.35 in

Mechanical Specifications

Minimum Bend Radius	75 mm 2.953 in
Minimum Bend Radius, furcation	10 mm 0.394 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

MFT-G24-AA-JA

Environmental Specifications

Operating Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Environmental Space

Indoor/Outdoor | Low Smoke Zero Halogen (LSZH)

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)