

RT-DF15-5-120



PIM-Guard High Capacity DUAL Non-Penetrating Roof Frame with Optimized Antenna Spacing 15 ft face, five 2-7/8 in OD x 120 in pipes

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating

Pipe, quantity 5

Dimensions

Height 3,048 mm | 120 in

Face Width 4.572 m | 15 ft

Width 4,572 mm | 180 in

Length 2.377 m | 7.8 ft

Pipe Length 3,048 mm | 120 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Pipe Outer Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ballast tray | Frame | Plain end pipes

RT-DF15-5-120

Packaging quantity 1
Weight, net 899.66 kg | 1,983.408 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code